Faital 3-Way Classic – 10" version (Faital 3WC 10")

Designed by Troels Gravesen

Can be built with either fabric dome (D2608/913000) or beryllium dome (SB29BAC-C000-4) tweeters



Click the buttons below to go to:

Price List

Complete Design Article

Contact / Purchase Form

Troels Gravesen's Introduction:

The moderate sized version of the popular Faital speakers with 10" bass driver delivering deep bass for the size.

Generally exceptional dynamics and transparency from moderate priced drivers - but with premium crossover components.

IMPORTANT!

Please read our sales terms to read about how the DIY kits are delivered and other important information.

Click HERE to read sales terms

Drivers used in the construction:

2 x Faital 10RS350 (8Ω) (Woofers)



2 x Faital 6RS140 (8 Ω) (Mid-range units)



2 x Scan-Speak D2608/913000 or SBA SB29BAC-C000-4 (Tweeters)



Beryllium dome - Crossover components:

Coils:

Litz Wire Wax Coils

Air & Iron Core Wire Coils



Tweeter capacitors:

Alumen Z-Caps



Mid-range capacitors:

Superior Z-Caps



Other positions:

Standard Z-Caps & MKT Z-caps



Resistors:

Superes (wire wound)



Fabric dome – Level 1 - Crossover components:

Coils:

Litz Wire Wax Coils

Air & Iron Core Wire Coils



Tweeter capacitors:

Alumen Z-Caps



Mid-range capacitors:

Superior Z-Caps



Other positions:

Standard Z-Caps & MKT Z-caps



Resistors:

Superes (wire wound)



Fabric dome – Level 2 - Crossover components:

Coils:

Air & Iron Core Wire Coils





Tweeter capacitors:

Superior Z-Caps



Mid-range capacitors:

Standard Z-Caps & Cross Caps



Other positions:

Standard Z-Caps & MKT Z-caps



Resistors:

Superes (wire wound)



Damping materials included in the DIY kit:

Damping felt

Polyester damping cloth



Combed natural wool filler



Accessories included in the DIY kit:

Binding post terminals (2 pairs)

Port tubes

Cables for internal wiring (PFTE/Silver)



Solder tag strips



Casco SuperFix component fastening glue



Screws for driver mounting

For general accessories click the box below



For SoundCare Super Spikes click the box below

